



# ULTRA LIGHT FILLER

## FILING AND SMOOTHING LIGHT READY MIXED

### TECHNICAL DEFINITION

Ultra-light ready mixed filler for repair of interior walls and ceilings. Shrink free and fast drying, ULTRA LIGHT FILLER is ideal for high quality filling jobs and is very ease to use.

### COMPOSITION AND APPEARANCE

Resins in emulsion with lightening agents and various additives.

The paste is snow white.

### ACCEPTED SUBSTRATES

Interior and exterior walls and ceilings:

- Plaster.
- Cellular concrete.
- Plasterboard.
- Wood.
- Masonry.
- Concrete.
- Roughcast.
- Cement render.

### TECHNICAL CHARACTERISTICS

- Density: 0.4.
- pH: 7.
- Shrink-free filling.
- Excellent application qualities.

### DOCUMENTS TO CONSULT

- DTU 59.1.
- NFT 36.608.

### PACKING

0.5 - 1 - 5 and 10 litres pails.

### STORAGE

12 months in unopened original packing protected from frost and extreme heat.

## APPLICATION

### PRECAUTIONS FOR USE

Do not apply in temperatures  $< +8^{\circ}\text{C}$  and  $> +35^{\circ}\text{C}$  and on frozen substrates.

### PREPARATION OF SURFACES

The substrates must be clean, free of dust and any trace of formwork release oil.

Indoors, during hot weather or on absorbent substrates the surfaces may be dampened slightly.

Cracks should be opened up before application.

### APPLICATION

Apply with putty knife or filling knife.

### CONSUMPTION:

Approximately  $0.4\text{ kg/m}^2/\text{mm}$  thickness.

### DRYING TIME

Depends on substrate, weather conditions and application thickness.

May be overpainted two hours after application in the case of filling hairline cracks and use with water based paints. Wait 24 hours for oil based paint.

## LIGHT READY MIXED

Ready to use **ULTRA LIGHT FILLER** product makes filling jobs easy.

**Shrink free, applied in one coat and fast drying. Allows shorter times between coats and speeds work on site.**


### ADVANTAGES

- Ready for use.
- No shrinkage or cracks.
- Quick drying.
- Ideal for jointing different types of substrate.

### APPLICATION TIP

**The filler can be made more flexible by working it between two spatulas.**

AFNOR classification: NFT 36.005.  
Family III – Class 2 c.



**Available in a box of 18 0.5-litre tubs**

